

# GalvinCare™ MH Anti-Ligature Solid Surface Recessed Washroom Shelf 500 x 200 x 125

**PRODUCT CODE:**

– 42100



## SPECIFICATIONS

- GalvinCare™ MH Anti-Ligature Solid Surface Recessed Washroom Shelf is made from a solid surface material comprised acrylic modified polyester resins, aluminium trihydrate fillers and colour granules.
- Ligature resistant.
- Vandal resistant.
- Hygienic and easily cleaned.
- Proven long-term product life.
- Anti-microbial solid surface.

## TECHNICAL DATA

Finish	Polar White
--------	-------------

*NOTE: Galvin Specialised continually strive to improve their products. Specifications may change without notice.*

## TOOLS AND SUPPLIES REQUIRED


- 4 x 1/4"- 20 wall anchors - 1000 lb pullout strength per anchor is required
- Construction Adhesive
- Anti-pick caulk
- Screwdriver
- Caulking gun






### PRE - INSTALLATION

Recessed Washroom Shelf must be fitted to a solid wall or other firm surface and installed by a qualified trades person.




- Make an opening in the wall of 465mm x 160mm.
- If necessary, re-enforce the structure of the wall.
- A piece of plywood behind the shelf is recommended to get good anchoring.






## INSTALLATION


**IMPORTANT:** Galvin Specialised products must be installed in accordance with these installation instructions and in accordance with your local regulatory requirements. Failing to comply with these provisions shall void the product warranty and may affect the performance of the product.




1. Put a modest amount of construction adhesive on the back rim of the shelf.



2. After the holes are marked and the anchors are in, fit the shelf in the opening and make sure it is level.



3. Screw the shelf to the wall in the pre-installed anchors



4. Put a bead of anti-pick caulking on the flat edge of the shelf.

## MAINTENANCE

- **Daily care:** wipe the surface with soapy water or a damp cloth.
- **Surface staining:** clean the surface with soapy water or ammonia-based cleansers.
- **Stubborn stains and superficial scratches:** clean the surface with an abrasive cleanser and a wet sponge.
- **Stubborn scratches:** sand with 400 grit sandpaper and then clean with an abrasive cleanser.
- AVOID contact with harsh chemicals such as drain cleansers and paint removers.
- AVOID contact with hot pots or heat producing appliances.

## WARRANTY

The warranty set forth herein is given expressly and is the only warranty given by the Galvin Engineering Pty Ltd. With respect to the product, Galvin Engineering Pty Ltd makes no other warranties, express or implied. Galvin Engineering Pty. Ltd. hereby specifically disclaims all other warranties, express or implied, including but not limited to the implied warranties of merchantability and fitness for a particular purpose.

Galvin Engineering Pty Ltd products are covered under our manufacturer's warranty available for download from [www.galvinengineering.com.au](http://www.galvinengineering.com.au) Galvin Engineering Pty Ltd expressly warrants that the product is free from operational defects in workmanship and materials for the warranty period as shown on the schedule in the manufacturer's warranty. During the warranty period, Galvin Engineering will replace or repair any defective products manufactured by Galvin Engineering without charge, so long as the terms of the Manufacturer's warranty are complied with.

The remedy described in the first paragraph of this warranty shall constitute the sole and exclusive remedy for breach of warranty, and Galvin Engineering Pty Ltd shall not be responsible for any incidental, special or consequential damages, including without limitation, lost profits or the cost of repairing or replacing other property which is damaged if this product does not work properly, other costs resulting from labour charges, delays, vandalism, negligence, fouling caused by foreign material, damage from adverse water conditions, chemical, electrical or any other circumstances over which Galvin Engineering has no control. This warranty shall be invalidated by any abuse, misuse, misapplication, improper installation or improper maintenance or alteration of the product.

*In the absence of a legal or industry definition of anti-ligature or ligature resistant products, when we use these terms, we are referring to products that are designed and manufactured with the intention of reducing the risk of ligature attachment to the product(s).*

*Galvin Engineering Pty Ltd will always endeavour to design and test our anti-ligature product(s) to reduce the risk of product ligature attachment that may result in serious injury or death.*

*Whilst all reasonable measures are taken at the time of design, the anti-ligature design of the products are not intended to and will not:*

- a. Replace protective measures that need to be taken in the specific circumstances of usage.*
- b. Substitute the need for supervision of those who may be at risk.*
- c. Protect and or prevent those at risk against any self-harm instances that may occur when installed; and*
- d. Protect and or prevent injury when the risks where unknown to us at the time of the design of the product(s).*

*Galvin Engineering Pty Ltd does not offer and does not represent or warrant that any product(s) for sale that are ligature-free.*

*Therefore, Galvin Engineering will not be liable for any claims, loss, or damages arising from ligature attachment on our products. It is the purchaser's responsibility to ensure that products purchased and installed are suitable for the environments in which they are installed, and suitable supervision and protective measures are in place to protect those at risk.*

